

Vario Couplings, Bohlender

2-part coupling for connecting elastic tubing such as Silikon®, Viton®, Tygon® etc. with non-elastic tubing made of glass, metal, PTFE or other plastics.


Functioning is as easy as it is ingenious. The elastic tubing is pushed on a cone and fixed on the actual coupling by means of a sleeve nut. A variety of threads are available for connecting at the other end of the non-elastic lines.

Ideally suited for use with tube pumps.

Type 1

With internal thread UNF 1/4" 28 G for connecting flared PTFE tubes in conjunction with a banjo bolt (supplied without tubing and without banjo bolt).

for tube inner Ø mm	suitable for wall thickness mm	Through bore mm	Connection thread	Order No.
0.8	0.8 and 1.6	0.8	UNF 1/4" 28 G	24 17 77808
1.6	0.8 and 1.6	1.6	UNF 1/4" 28 G	24 17 77816



Type 2

With external GL thread for connecting BOLA laboratory screw joints. These must be ordered separately according to the outside diameter of the tubing.

for tube inner Ø mm	suitable for wall thickness mm	Through bore mm	Connection thread GL	Order No.
0.8	0.8 and 1.6	0.8	14	24 17 68108
1.6	0.8 and 1.6	1.6	14	24 17 68116
3.2	1.6	3.2	14	24 17 68124
4.0 and 4.8	1.6	4.0	14	24 17 68132
6.4	1.6	6.4	18	24 17 68140
8.0 and 9.5	1.6 and 2.4	8.0	18	24 17 68148
11.0	1.6 and 2.4	12.7	25	24 17 68156
12.7	1.6 and 2.4	12.7	25	24 17 68164

