

Eye Wash Bottles, EKASTU

EKASTU eye wash bottles

Eye wash bottles are used to rinse the eyes in the frame of first aid following an accident involving the eyes. Use of an eye wash bottle does not replace an ophthalmological examination, but can help to minimize injuries. The filled EKASTU eye rinsing bottles are eye wash units without water connection, according to the standard DIN EN 15154-4. All filled eye wash bottles are medical products. The bottles are made of transparent polyethylene (PE) and are leak-proof. The eye funnel optimally encloses the eye socket and at the same time guarantees a safe and protected contact with the eyeball. During rinsing, water collects in the funnel, which forms a rinsing bath. Contaminated water flows out through a separate outlet. The EKASTU eye rinsing bottles of the MINI series are ideal for carrying in breast or coat pockets.



Article	Order No.
① Eye wash bottle ECO with funnel, full, approx. 600 ml	10 52 37111
② Eye wash bottle ECO-MINI with funnel, full, approx. 200 ml	10 52 37112
Eye wash bottle ECO with funnel, empty, approx. 600 ml	10 52 37011
Eye wash bottle ECO-MINI with funnel, empty, approx. 200 ml	10 52 37012
③ Eye wash station (EPS), complete with 2 EKASTU eye wash bottles approx. 200 + 600 ml	10 52 37999

Accessories

Article	Order No.
Eye wash station (EPS), empty for 2 EKASTU eye wash bottles	10 52 37955
④ Wall box with transparent lid for 1 eye wash bottle	36 52 20120
⑤ Wall holder for 1 eye wash bottle	10 52 37950

